

**dual
pumps**

Gum Blaster



*Removes a sticky
problem FAST!*



Gum Blaster

Chewing gum contamination is a problem that is here to stay. For years the search has been on to find the definitive gum removal system, many have been developed to remove this sticky problem, but none have provided the complete answer.

The traditional method of using a pressure washer lance is slow, painstaking and leaves a lot of mess to clean up afterwards, including the gum that has just been removed.

Now a unique accessory is available that not only removes the gum, but collects it at the same time, **the amazing Gum Blaster!!!**

The **Gum Blaster** is easy to operate and can be used with most hot pressure washers.

We recommend a minimum pressure of 150 Bar & 12 Lpm.

Not supplied with gun or lance assembly



it's as easy as..1, 2, 3

1



2



3



- 1 Position the Gum Blaster over the chewing gum
- 2 Pull the trigger
- 3 The gum is instantly removed & held in the collection chamber

Part No.	Nozzle Size	Max Press	Max Temp	Weight	Inlet
99.9721.045	045	250 Bar	90°C	2.0 Kg	22mm M
99.9721.055	055	250 Bar	90°C	2.0 Kg	22mm M
Dimensions - Length 280mm - Height 180mm - Width 130mm					